



## Pocket Pro+ ORP Tester with Replaceable Sensor

**Product #:** 9532100  
**ZAR Price:** Contact Hach  
**Ships within 1 week**

### Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ deliver accurate results with built in diagnostics, replaceable batteries, and a large, easy-to-read LCD screen.

#### Confidence in results

Take the guesswork out of when to calibrate or clean the sensor with built-in diagnostics

#### Save time and money

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

#### Ease of use

Large LCD screen is easy to read and backlight included in replacement sensor models allow for taking measurements in almost any environment

---

### Specifications

Accuracy:	2 mV
Accuracy 2:	2 mV
Backlight:	Yes
Battery requirements:	4, AAA
IP Rating:	IP67
Manual Languages:	English, French, German, Italian, Spanish
Operating temperature range:	0 - 50 °C
Parameter:	ORP
Range:	±999 mV
Resolution:	1 mV
Sample Volume:	9 mL
Warranty:	12 months
What's included?:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.

---

### What's included?

Includes: tester, 4 AAA batteries, lanyard and quick start guide.