



## Pitcher, graduated, 1000 cc

<b>Product #:</b>	<b>2612853</b>
ZAR Price:	Contact Hach
Ships within 2 weeks	

Chemical-resistant, shatter-proof, tall-form pitchers with well-designed spouts, and large handles. Metric graduations are molded onto outside wall of each pitcher. Polypropylene, steam autoclavable at 250°F (121°C).

---

### Specifications

Capacity:	1000 mL
Depth:	167 mm
Graduations:	50 mL
Quantity:	1 each