



Pump, Vacuum/Pressure, Portable, 220v, 60 Hz

Product #:	2824801
ZAR Price:	Contact Hach
Ships within 1 week	

Provides up to 68.6 cm (27") Hg vacuum for applications in laboratory, office or industrial plant—vacuum distillation, filtration, and air pollution studies employing membrane filters. Quiet, pulse less air delivery and vacuum. Compact dimensions (WxDxH) 15x39x20 cm

(6x15.4x8 inches). Complete with vacuum and pressure gauges and regulators, hose nipples, outlet filter, switch, cord, and plug. Capacity: 0.6 liters/sec (1.3 cfm) at 0 mm Hg. 124 W (1/6 HP).

Specifications

Electrical Specifications:	230 Vac, 60 Hz NA Plug
Length:	203 mm
Quantity:	1 each