



Hot plate, 7x7 in., digital, 115 Vac

Product #: 2881500
ZAR Price: Contact Hach
Available

Cimarec Ceramic top, 7 x 7 in. hot plate features a reflective, white ceramic that is seamless, easy to clean, and resistant to alkali/acid solutions. Low profile increases efficiency and reduces spill risk. Easy-to-read digital temperature settings features a flashing warning (CAUTION! HOT TOP) when the surface exceeds 50°C. Low-profile design to improve safety. Detachable cord. Built-in support rod holder (order support rod separately). Operating temperature range: 5 to 540°C (41 to 1004°F).

Ceramic top

Easy to clean and resists alkalis and acids. Seamless, reflective white surface aids in sample visibility.

Rugged design

Low-profile and stable, rugged base prevents tipping and spillage. Cast-aluminum base diverts spills from internal electronics.

Maintains temperature

Microprocessor controls with feedback technology maintain consistent repeatable temperature settings.

Integrated ring-stand holder

To accommodate 1.3cm (0.5 in) diameter support rods.

Easy to read adjustments

Digital display and large control knob enable precise temperature control. Hot surface alert minimizes accidents.

Specifications

| | | |
|----------------------------|--------------|---|
| Ceramic Top | Dimensions : | 7.25 x 7.25" |
| | | (18.4 x 18.4 cm) |
| Electrical Specifications: | | 120 / 8.8 / 1060 |
| Power: | | 115 Vac, 60 Hz |
| Quantity: | | 1 each |
| Special Features: | | Hot plate, 7 x 7 |
| Type: | | Hot plate |
| What's included?: | | Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar. |

What's included?

Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.