



## Hot Plate Stirrer, 7x7 in., digital, 115 Vac

**Product #:** 2881600  
**ZAR Price:** Contact Hach  
**Ships within 1 week**

Cimarec Ceramic top, 7 x 7in. hot plate stirrer features a reflective, white ceramic that is seamless, easy to clean, and resistant to alkali/acid solutions. Low profile increases efficiency and reduces spill risk. Easy-to-read digital temperature settings features a flashing warning (CAUTION! HOT TOP) when the surface exceeds 50°C. Low-profile design to improve safety. Detachable cord. Built-in support rod holder (order support rod separately). Operating temperature range: 5 to 540°C (41 to 1004°F) Stirring range of 60-1200 RPM.

### Ceramic top

Easy to clean and resists alkalis and acids. Seamless, reflective white surface aids in sample visibility.

### Rugged design

Low-profile and stable, rugged base prevents tipping and spillage. Cast-aluminum base diverts spills from internal electronics.

### Constant speed and maintains temperature

Microprocessor-controlled feedback technology maintains consistent, repeatable temperature settings from 5°C up to maximum.

### Integrated ring-stand holder

To accommodate 1.3cm (0.5 in) diameter support rods.

### Easy to read adjustments

Digital display and large control knob enable precise temperature control. Hot surface alert minimizes accidents.

---

## Specifications

Ceramic Top	Dimensions :	18.4 x 18.4 cm (7.25" x 7.25")
Electrical Specifications:		120 / 8.9 / 1070
Power:		115 Vac, 60 Hz
Quantity:		1 each
Special Features:		Stirrer, Hot plate
Type:		Hot plate/Stirrer
What's included?:		Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.

---

## What's included?

Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.