



## Lamp, Ultraviolet, Long-Wave 115 Vac, 60 Hz

**Product #:**

**2184300**

**Contains mercury. Dispose of according to local, state and federal regulations.**

**ZAR Price:**

Contact Hach

**Ships within 2 weeks**

Mid-size (6 Watt) high intensity, hand-held and line-operated. Intensity at 15.2 cm (6"), 750  $\mu\text{W}/\text{cm}^2$ . Filters: Two 6 x 7.6 cm (2.4 x 3") in snap on/off frame. Overall dimensions: 37.5 x 8.9 x 6.7 cm (14.8 x 3.5 x 2.6"). Weight: 0.91 kg (2 lbs). UL listed. Meets existing OSHA electrical standards. 365 nm. UV goggles (PN 2113400) not included.

---

### Specifications

Quantity: 1

---

### Required Accessories

- Goggles, ultraviolet (Item 2113400)