



FH950 Portable Velocity/Depth Sensor, 20' Cable

Product #: EM950.1020
ZAR Price: Contact Hach
No availability shown

The FH950's electromagnetic velocity sensor with 6.5' cable has no moving parts and never requires maintenance, making it one of the lowest maintenance solutions on the market. Turbulent, noisy and low velocities are easily metered. When the sensor is placed in flowing water, its magnetic field creates a voltage that is sensed by electrodes embedded in the sensor. The voltage amplitude, proportional to the water velocity flowing around the sensor, is electronically processed by the smart sensor's microprocessor and is digitally transmitted through the cable to the portable meter display. Portable hand-held meter sold separately.

One of the lowest maintenance solutions on the market

Electromagnetic sensor has no moving parts and never requires mechanical maintenance

Accurate even in difficult monitoring sites.

The FH95's sensor easily monitors turbulent, noisy and low velocity applications.

Specifications

Accuracy 2:	$\pm 2\%$ of reading ± 0.05 ft/s (± 0.015 m/s) through the range of 0 - 10 ft/s (0 - 3.04 ms/s); $\pm 4\%$ of reading from 10 - 16 ft/s (3.04 - 4.87 m/s)
	DEPTH The larger of $\pm 2\%$ of reading or ± 0.504 in (0.015 m). Steady state temperature and static non-flowing water.
Cable Length:	20 ft
Electrode Type:	Velocity & Depth
Method:	VELOCITY - Electromagnetic
	DEPTH - Diaphragm type: absolute pressure with single point calibration
Operating temperature range:	-20 - 55 °C
Range:	0 - +20
Resolution:	VELOCITY: 0.01 value < 100 0.1 value < 1000; 1.0 value > 1000
Warranty:	12 months
What's included?:	1 each portable velocity/depth sensor

What's included?

1 each portable velocity/depth sensor