



Sipper Module DR5000

Product #: LZV485

OBSOLETE ITEM
This item is no longer available.

Sipper Module for serial analytics with 1 cm Pour-thru cell (quartz), tube set Silikor

Specifications

Flow Rate:	1 mL/s (nominal)
Height:	290 mm
Includes:	Sipper Module, LZV780 Tube Set
	1 cm rectangle pour-thru cell 160 µl
Max. operating humidity:	95 %
Max. Storage Humidity:	85 %
Storage conditions:	-17 °C to 60 °C
Wavelength Range:	190 - 1100 nm
Weight:	1.6 kg