



Pocket Pro ORP Tester

Product #: 9531100
ZAR Price: Contact Hach
Ships within 2 weeks

Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ deliver accurate results with built in diagnostics, replaceable batteries, and a large, easy-to-read LCD screen.

Confidence in results

Take the guesswork out of when to calibrate or clean the sensor with built-in diagnostics

Save time and money

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

Ease of use

Large LCD screen is easy to read and backlight included in replacement sensor models allow for taking measurements in almost any environment

Specifications

Accuracy:	± 2 mV
Backlight:	No
Battery requirements:	4, AAA
Calibration:	Auto
IP Rating:	IP67
Manual Languages:	English, French, German, Italian, Spanish
Operating temperature range:	0 - 50 °C
Parameter:	ORP
Range:	±999 mV
Resolution:	1 mV
Sample Volume:	7 mL
Warranty:	12 months
What's included?:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.

What's included?

Includes: tester, 4 AAA batteries, lanyard and quick start guide.