



## Pocket Pro Low Range Conductivity Tester

**Product #:** 9531400  
**ZAR Price:** Contact Hach  
**Ships within 2 weeks**

### Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ deliver accurate results with built in diagnostics, replaceable batteries, and a large, easy-to-read LCD screen.

#### Confidence in results

Easy calibration steps take the guesswork out of calibrating the sensor to keep it in optimum condition.

#### Save time and money

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

#### Ease of use

The large LCD screen is easy to read; backlighting is included on Pocket Pro<sup>+</sup> models, allowing measurement in almost any lighting environment.

---

### Specifications

Accuracy:	1% FS
Backlight:	No
Battery requirements:	4, AAA
IP Rating:	IP67
Manual Languages:	English, French, German, Italian, Spanish
Operating temperature range:	0 - 50 °C
Parameter:	LR Conductivity, Temp
Range:	0 - 1990 µS/cm
Resolution:	1 µS/cm
Sample Volume:	7 mL
Warranty:	12 months
What's included?:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.

---

### What's included?

Includes: tester, 4 AAA batteries, lanyard and quick start guide.