



Pocket Pro High Range Conductivity Tester

Product #: 9531500
ZAR Price: Contact Hach
Ships within 2 weeks

Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ deliver accurate results with built in diagnostics, replaceable batteries, and a large, easy-to-read LCD screen.

Confidence in results

Easy calibration steps take the guesswork out of calibrating the sensor to keep it in optimum condition.

Save time and money

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

Ease of use

The large LCD screen is easy to read; backlighting is included on Pocket Pro⁺ models, allowing measurement in almost any lighting environment.

Specifications

Accuracy:	2% FS
Backlight:	No
Battery requirements:	4, AAA
IP Rating:	IP67
Manual Languages:	English, French, German, Italian, Spanish
Model:	Pocket Pro Conductivity _{HR}
Operating temperature range:	0 - 50 °C
Parameter:	HR Conductivity, Temp
Range:	0.0 - 19.99 mS/cm
Resolution:	0.01 mS/cm
Sample Volume:	7 mL
Warranty:	12 months
What's included?:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.

What's included?

Includes: tester, 4 AAA batteries, lanyard and quick start guide.