



MP-6p Portable cableless multimeter

Product #:

HMP6P

ZAR Price:

Contact Hach

Ships within 3 days

Cableless!

With integrated sample cups and internal sensors for conductivity, pH, ORP, temperature, TDS, and mineral/salt measurements.

Easy-to-use cableless meter for portable spot checks of clean water applications and tap sampling. With simple one-handed operation, the meter allows to “dip and go” for rapid testing.

Specifications

Accuracy:	Conductivity, TDS, Mineral/Salt:
	± 1 % of reading
Accuracy 2:	Temperature:
	± 0.1 °C
Accuracy 3:	pH:
	± 0.01 pH
Accuracy 4:	ORP/Redox:
	± 0.1 mV
Backlight:	-
Compliance Certifications:	CE.WEEE
Conductivity resolution:	0.01 (<100 µS/cm), 0.1 (<1000 µS/cm), 1.0 (<10 mS/cm), 0.01 (<100 mS/cm), 0.1 (<200 mS/cm)
Dimensions (H x W x D):	64 mm x 69 mm x 196 mm
Filling Solution:	-
GLP Features:	-
Inputs:	-
Interface Languages:	English
Internal Data Storage:	100
IP Rating:	IP67 / NEMA 6
ISA Required:	-
Kit Option:	Instrument Only
Kit?:	No

Length:	196 mm
Manual Languages:	English, French, German, Italian, Spanish, Chinese, Portuguese, Dutch, Swedish, Turkish, Danish, Polish, Czech, Hungarian, Croatian, Romanian, Bulgarian, Greek, Russian
Material:	Housing: VALOX*
Measuring range conductivity:	0 - 9999 µS/cm
Measuring range mineral/salt:	10 - 200 ppt
Measuring Range ORP:	± 999 mV
Measuring range pH:	0 - 14 pH
Measuring Range TDS:	0 - 9999 ppm
Measuring Range TDS 2:	10 - 200 ppt
Measuring Range Temperature:	0 - 71 °C
Memory:	100
Mineral/Salt resolution:	0.01 (<100 ppm)
Mineral/Salt resolution 2:	0.1 (<1000 ppm)
Mineral/Salt resolution 3:	1.0 (<10 ppt)
Mineral/Salt resolution 4:	0.01 (<100 ppt)
Mineral/Salt resolution 5:	0.1 (<200 ppt)
Model:	MP-6
Outputs:	IR
Parameter:	pH, ORP, Conductivity, TDS, Salinity, Temp
PC Data Transfer Software :	#
pH Resolution:	0.01 pH
Range:	pH: 0 - 14 pH ORP: ±999 mV Cond.: 0.01 µS/cm - 200 mS/cm Resist.: - TDS: 0.01 ppm - 200 ppt Mineral/Salt: 0.01 ppm - 200 ppt
Sample Volume:	pH/ORP: ml
Sensor Type :	pH: Glass ORP: Pt Cond.: 4-cell (316 Stainless Steel)
Special Features:	Portable Meter
Specifications:	MP-6p Portable meter with internal sensors
Standard storage temperature:	0 - 55 °C
TDS Resolution:	0.01 (<100 ppm)

TDS Resolution 2:	0.1 (<1000 ppm)
TDS Resolution 3:	1.0 (<10 ppt)
TDS Resolution 4:	0.01 (<100 ppt)
TDS Resolution 5:	0.1 (<200 ppt)
Temperature Compensation:	Automatic 0 - 71 °C
Temperature Correction Factor:	0 - 9.99
Temperature Range:	0 - 71 °C (32 - 160 °F)
Temperature resolution:	0.1 °C
Warranty:	12 months
Weight:	0.352 kg