



Sension+ 5202 pH liquid filled combination electrode with screw cap S7 for general use.

Product #: LZW5202.97.0002

ZAR Price: Contact Hach

pH liquid electrode (refillable) with ceramic diaphragm. Glass body. Range 0-12 pH, 0 to 80 °C. S7 screw cap.

Large, semi spheric membrane, very robust and fast responding.

This pH electrode is suitable for aqueous media in general. Fast responding due to the robust, large and semi spheric pH membrane.

Fast responding due to large, semi spheric pH membrane.

Specifications

Accuracy:	0.002 pH with MM340 Meter
Connector:	Screw cap S7
Dimensions (D x L) :	12 mm x 130 mm
Electrode Type:	Laboratory
Filling Solution:	LZW9500.99 KCl 3M
Length:	130 mm
Material:	Sensor Body: Glass
Parameter:	pH
Probe Junction :	Ceramic
Range:	0 - 12 pH
Sensor Type :	Large, semi-spheric glass membrane.
Temperature Range:	0 - 80 °C
Warranty:	12 months

Required Accessories

- AS7 cable / 1M / BNC for instruments w/ BNC connector (Item LZW9055.99)