



Hach AE Grade Filters, 90 mm, 100/pk

Product #:	2551459
ZAR Price:	Contact Hach
Ships within 1 week	

Hach Grade AE filters are comparable to Pall Type A/E filters, with a diameter of 90 mm. These filters feature fast flow rates, fine porosity and particle retention of 1.1µm which make them ideal for many dissolved and suspended solids testing procedures including Standard Methods 2540 C, 2540 D and 2540 E.

This binder-free, borosilicate glass microfiber filter has a DOP (Diethyl phthalate) efficiency of 99.98% and a maximum operating temperature of 550°C in air.

Specifications

Diameter:	90 mm
Material:	Glass Microfiber
Pore Size:	1.0 µm
Quantity:	100 /pk