



Filters, Hach 934-AH, 90 mm, 100/pk

Product #:	2511210
ZAR Price:	Contact Hach
Available	

Hach 934-AH Filters are specified for use in Standard Methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5 μ m particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500°C which is a unique and especially important feature for laboratories performing Fixed and Volatile Solids analysis of water and wastewater.

934-AH is a registered trademark of Whatman, Inc./GE Healthcare and used under license.

Specifications

Diameter:	90 mm
Material:	Glass Microfiber
Pore Size:	1.5 μ m
Quantity:	100 /pk
Units:	100/pk