



## ValuSep SPE Filter, 90 mm, 50/PK

<b>Product #:</b>	<b>2947802</b>
ZAR Price:	Contact Hach
Available	

ValuSep SPE Filters for EPA Method 1664A are designed to provide high recovery and low blank values in Horizon SPEDEX and SPE Manifold applications. Chemically treated with a proprietary reverse phase adsorbent, single layer borosilicate glass ValuSep SPE Filters (47mm) can filter the 40 mg/L EPA PAR standard in approximately 10 minutes with significantly faster filtration times

for 1 L NPDES-type samples. ValuSep SPE Filters offer high recoveries and low blanks at a great price.

---

### Specifications

Diameter:	90 mm
Quantity:	50 /pk
Units:	50/pk