



## Hach 934-AH Filters, 24mm, 100/pk

<b>Product #:</b>	<b>2511202</b>
ZAR Price:	Contact Hach
Available	

Hach 934-AH Filters are specified for use in Standard methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5  $\mu\text{m}$  particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500°C, which is a unique and especially important feature for laboratories performing Fixed and Volatile Suspended Solids analysis of water and wastewater.

*The trademark 934-AH is owned by GE Healthcare/Whatman Inc. and used under exclusive license for purposes of private label.*

---

### Specifications

Diameter:	24 mm
Material:	Glass Microfiber
Pore Size:	1.5 $\mu\text{m}$
Quantity:	100 /pk
Units:	100/pk