



Prefilters, Glass Fiber (5µm)

Product #:

2947826

OBSELETE ITEM

This item is no longer available.



Items with this mark may be considered hazardous under some shipping conditions.

If necessary, we will change your selected shipping method to accomodate these items.

Xenosep brand ValuSep SPE Filters for EPA Method 1664A are designed to provide high recovery and low blank values in Horizon SPEDEX and SPE Manifold applications. Chemically treated with a proprietary reverse phase adsorbent, single layer borosilicate glass ValuSep SPE Filters (47mm) can filter the 40 mg/L EPA PAR standard in approximately 10 minutes with significantly faster filtration times for 1 L NPDES-type samples. ValuSep SPE Filters offer high recoveries and low blanks at a great price.

Specifications

Diameter:	100 mm
Material:	Glass Microfiber
Package size UOM:	pk
Pore Size:	5.0 µm
Quantity:	50 /pk
Units:	50/pk