



## Hot plate, 4x4, digital, 115V, North American plug. NO CE MARK.

**Product #:** 2881400  
**ZAR Price:** Contact Hach  
**Available**

Cimarec Ceramic top, 4 x 4 hot plate features a reflective, white ceramic that is seamless, easy to clean, and resistant to alkali/acid solutions. Low profile increases efficiency and reduces spill risk. Easy-to-read digital temperature settings features a flashing warning (CAUTION! HOT TOP) when the surface exceeds 50°C. Low-profile design to improve safety. Detachable cord. Built-in support rod holder (order support rod separately). Operating temperature range: 5 to 540°C (41 to 1004°F).

### Ceramic top

Easy to clean and resists alkalis and acids. Seamless, reflective white surface aids in sample visibility.

### Rugged design

Low-profile and stable, rugged base prevents tipping and spillage. Cast-aluminum base diverts spills from internal electronics.

### Maintains temperature

Microprocessor controls with feedback technology maintain consistent repeatable temperature settings.

### Integrated ring-stand holder

To accommodate 1.3cm (0.5 in) diameter support rods.

### Easy to read adjustments

Digital display and large control knob enable precise temperature control. Hot surface alert minimizes accidents.

---

## Specifications

Ceramic Top	Dimensions :	4.25 x 4.25"
		(10.8 x 10.8 cm)
Electrical Specifications:		120 / 3.2 / 385
Power:		115 Vac, 60 Hz
Quantity:		1 each
Special Features:		Hot plate, 4 x 4
Type:		Hot plate
What's included?:		Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.

---

## What's included?

Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.