



Ceramic Top Magnetic Stirrer, 7x7 in., 115 Vac

Product #: 2881300
ZAR Price: Contact Hach
Ships within 1 week

Cimarec Ceramic top 7 x 7 in. stirrer features a reflective, white ceramic surface that is seamless, easy to clean, and resistant to alkali/acid solutions. Low profile increases efficiency, and reduces spill risk. StirTrac™ technology offers improved slow speed stirring, consistent speed control, adjustable speed range from 50-1200 RPM, and rapid braking. Detachable cord. Integral ringstand/support rod holder (order rod separately).

Ceramic top

Easy to clean and resists alkalis and acids. Seamless, reflective white surface aids in sample visibility.

Rugged design

Low-profile and stable, rugged base prevents tipping and spillage. Cast-aluminum base diverts spills from internal electronics.

Constant speed

Microprocessor feedback control provides constant speed regardless of changes in viscosity and prevents runaway and magnetic decoupling. Direct-drive motor and magnet system permits quiet stirring.

Integrated ring-stand holder

To accommodate 1.3cm (0.5 in) diameter support rods.

Specifications

Ceramic Top	Dimensions :	7.0 x 7.0"
Electrical Specifications:		120 Vac, 50/60 Hz
Power:		115 Vac, 60 Hz
Quantity:		1 each
Special Features:		Stirrer, Ceramic Top Magnetic
Type:		Stirrer
What's included?:		Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.

What's included?

Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.