



Hot plate stirrer, 7 x 7 in., digital, 230 Vac

Product #: 2881602
ZAR Price: Contact Hach
Ships within 3 days

Cimarec Ceramic top, 7 x 7 in. hot plate stirrer features a reflective, white ceramic that is seamless, easy to clean, and resistant to alkali/acid solutions. Low profile increases efficiency and reduces spill risk. Easy-to-read digital temperature settings features a flashing warning (CAUTION! HOT TOP) when the surface exceeds 50°C. Low-profile design to improve safety. Detachable cord. Built-in support rod holder (order support rod separately). Operating temperature range: 5 to 540°C (41 to 1004°F) Stirring range of 60-1200 RPM.

Ceramic top

Easy to clean and resists alkalis and acids. Seamless, reflective white surface aids in sample visibility.

Rugged design

Low-profile and stable, rugged base prevents tipping and spillage. Cast-aluminum base diverts spills from internal electronics.

Constant speed and maintains temperature

Microprocessor-controlled feedback technology maintains consistent, repeatable temperature settings from 5 °C up to maximum.

Integrated ring-stand holder

To accommodate 1.3 cm (0.5 in) diameter support rods.

Easy to read adjustments

Digital display and large control knob enable precise temperature control. Hot surface alert minimizes accidents.

Specifications

Ceramic Top	Dimensions :	18.4 x 18.4 cm (7.25" x 7.25")
Electrical Specifications:		220-240 / 4.9 / 1170
		CE Marked
Power:		230 Vac, 50 Hz
Quantity:		1 each
Special Features:		Hot plate, 7 x 7
Type:		Hot plate/Stirrer