



Hot Plate Stirrer, 7x7 in., digital, 115 Vac

Product #: 2881600
ZAR Price: Contact Hach
Ships within 1 week

Cimarec Ceramic top, 7 x 7in. hot plate stirrer features a reflective, white ceramic that is seamless, easy to clean, and resistant to alkali/acid solutions. Low profile increases efficiency and reduces spill risk. Easy-to-read digital temperature settings features a flashing warning (CAUTION! HOT TOP) when the surface exceeds 50°C. Low-profile design to improve safety. Detachable cord. Built-in support rod holder (order support rod separately). Operating temperature range: 5 to 540°C (41 to 1004°F) Stirring range of 60-1200 RPM.

Ceramic top

Easy to clean and resists alkalis and acids. Seamless, reflective white surface aids in sample visibility.

Rugged design

Low-profile and stable, rugged base prevents tipping and spillage. Cast-aluminum base diverts spills from internal electronics.

Constant speed and maintains temperature

Microprocessor-controlled feedback technology maintains consistent, repeatable temperature settings from 5°C up to maximum.

Integrated ring-stand holder

To accommodate 1.3cm (0.5 in) diameter support rods.

Easy to read adjustments

Digital display and large control knob enable precise temperature control. Hot surface alert minimizes accidents.

Specifications

Ceramic Top	Dimensions :	18.4 x 18.4 cm (7.25" x 7.25")
Electrical Specifications:		120 / 8.9 / 1070
Power:		115 Vac, 60 Hz
Quantity:		1 each
Special Features:		Stirrer, Hot plate
Type:		Hot plate/Stirrer
What's included?:		Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.

What's included?

Includes: Detachable line cord and plug. All models supplied with a 0.38 dia. x 2 in.L (1 x 5.1cm) TFE-coated stir bar, except 4 x 4 in., which includes a 1 in. (2.54cm) stir bar.