



Blender, Two Speed, 1.2 L, 120 Vac-50/60 Hz

Product #:	2616100
ZAR Price:	Contact Hach
Ships within 1 week	

This blender is tough enough to handle homogenizing wastewater, sludge, soil or heavy weight food samples for superior analytical results. Both models have thick walled glass containment jars and durable, rust free stainless steel blades. Two-piece vinyl and styrene lid.

Specifications

Electrical Specifications:	120 Vac, 50/60 Hz
Instrument:	All except DR/4000, PC II
Method:	8006
Quantity:	1 each