



Blender, Two Speed, 1.2 L, 240 Vac-50/60 Hz

Product #:

2616102

 **Hazardous**

OBSOLETE ITEM

This item is no longer available.

Items with this mark may be considered hazardous under some shipping conditions.

If necessary, we will change your selected shipping method to accomodate these items.

This blender is tough enough to handle homogenizing wastewater, sludge, soil or heavy weight food samples for superior analytical results. Both models have thick walled glass containment jars and durable, rust free stainless steel blades. Two-piece vinyl and styrene lid.

Specifications

Electrical Specifications:	240 Vac, 50/60 Hz
Instrument:	All except DR/4000, PC II
Method:	8006
Quantity:	1 each