



## Still, Automatic, 120 Vac, 50/60 HZ

<b>Product #:</b>	<b>2615900</b>
ZAR Price:	Contact Hach
Ships within 2 weeks	

The easy-to-use Barnstead/Thermolyne FI-Streem II 2S Glass Still provides low volumes (2.0 liters per hour) of high-quality distilled water. The still removes both inorganic and organic impurities. Patented vapor trap eliminates carry-over of vapor-borne water droplets which may contain impurities. The still's space-saving design allows for wall or benchmounting. The still has fully automatic controls, a level sensor, and dual feed capability. CSA approved. Pressure: 10-80 psi. Dimensions: 79 x 26 x 32.5 cm (31.5 x 10.5 x 13"). Shipping weight: 15 kg (33 lbs).