



TU5400sc Ultra-High Precision Low Range Laser Turbidimeter with Flow Sensor, Automatic Cleaning, RFID, and System Check, EPA Version with SC200 Controller, 24 VDC, 1 Channel

Product #: 2979855

OBSOLETE ITEM
This item is no longer available.

The next standard in the evolution of turbidity

The EPA approved TU5 Series platform employs a unique optical design that sees more of your sample than any other turbidimeter, delivering the best low level precision and sensitivity while minimising variability between measurements. For the first time you will be able to remove uncertainty of which measurement to trust between your lab and process instruments, thanks to identical 360° x 90° Detection Technology in any TU5 Series turbidimeter.

The TU5400sc Ultra-High Precision Low Range Laser Turbidimeter dramatically reduces the time needed to get a turbidity measurement you can rely on. A stable laser light source eliminates the need for annual lamp replacements. The turbidimeter's measurement surface area has been reduced by 98%, allowing you to save time cleaning. An automatic cleaning module is available that keeps your instrument clean, reducing the amount of time spent cleaning the instrument ever further. All of this, along with the ability to measure to 0.2 mNTU, gives you the next standard in the evolution of turbidity.

Only the new TU5 Series Lab & Process Turbidimeters with 360° x 90° Detection deliver unprecedented confidence that a change in your reading is a change in your water.

Groundbreaking 360° x 90° Detection Technology

The TU5 Series employs a unique optical design that sees more of your sample than any other turbidimeter, delivering the best low level precision and sensitivity while minimizing variability from test to test.

Matching lab and online results

For the first time you will be able to remove the uncertainty of which measurement to trust, thanks to identical 360° x 90° Detection Technology in both instruments.

Everything about turbidity – faster

The TU5 Series dramatically reduces the time needed to get a turbidity measurement you can rely on, with 98% less online sample surface area to clean, sealed vials for calibration, and the elimination of the need for indexing and silicone oil in the lab. Not to mention, a smaller online sample volume means you will detect events almost immediately.

No surprises

Prognosys monitors your TU5 Series online instrument, proactively alerting you to maintenance needs before your measurement becomes questionable. And a Hach Service Agreement protects your investment and helps ensure that you stay in compliance and on budget.

Specifications

Accuracy:	±2% of reading plus 0.01 NTU from 0 - 40 NTU
Cable Length:	1.6 m, extendable up to 50 m for instrument without accessories
Calibration Method:	For Formazin and Stablcal:

20 NTU from 0 - 40 NTU; at 20 FNU and 600 NTU for full range

Custom calibration for up to 6-point calibrations

Certifications:

CE compliant

US FDA accession number: 1420493-000 EPA version, 1420492-000 ISO version

Australian ACMA Marking

Channels:

1

Communication:

System Check & RFID

Controller:

1 Channel, 24 VDC

Controller Options:

Yes

Dimensions (H x W x D):

249 mm x 268 mm x 190 mm

Enclosure rating:

Electronic compartment IP55; all other functional units IP65 with process head/ACM attached to the TU5300sc/TU5400sc instrument

Fitting:

Sample quick connector: ¼-in. for ¼-in. tubing

Instrument:

With Flow Sensor and Automatic Cleaning Module

Light source:

Class 2 laser product, with embedded 650 nm (EPA 0.43 mW) or Class 1 laser product, with embedded 850 nm (ISO), max. 0.55 mW (complies with IEC/EN 60825-1 and to 21 CFR 1040.10 in accordance with Laser Notice No. 50)

Lower Limit of Detection (LOD):

0.0001 NTU

Material:

ASA S 777K / RAL7000, TPE RESIN Elastocon STK40,

Thermoplastic Elastomer TPS-SEBS

Model:

TU5400sc

Mounting Configurations:

Wall Mount

Operating Humidity:

Relative humidity: 5 - 95% at different temperatures, non-condensing

Operating temperature range:

0 - 50 °C

Options:

Process Head, Flow Sensor, & Automatic Cleaning Module

Power requirements (Voltage):

24 VDC

Range:

EPA:

0 - 700 NTU / FNU / TE/F / FTU

0 - 175 EBC

Regulatory:

EPA

Repeatability:

Better than 1% of reading or ±0.0006 NTU on Formazin at 25 °C (77 °F), whichever is greater

Resolution:

0.0001 NTU / FNU / TE/F / FTU / EBC

Response time:

T90 <30 seconds at 100 mL/min

Sample Flow Rate:

100 - 1000 mL/min; optimal flow rate: 200 - 500 mL/min

Sample Pressure:

6 bar (87 psi) maximum, compared to air at sample temperature range from 2 - 40 °C (35.6 - 104 °F)

Sample Temperature:

2 to 60 °C (35 to 140 °F)

Signal Average Time:

1 to 90 seconds

Storage conditions:

-40 to 60 °C (-40 to 140 °F)

Stray Light:

<10 mNTU

System Check:

Yes

Units:

NTU, FNU, TE/F, FTU, EBC

Verification:

Liquid: Stablcal, Formazin (0.1 - 40 NTU)

	Dry: Glass Rod at <0.1 NTU
Warranty:	12 months
Weight:	2.7 kg (5.0 kg with all accessories)
What's included?:	TU5400sc Turbidimeter, User Manual, Wall Mount, Vial Replacement Tool, Screw Set, Drying Cartridge, Flow Regulator, Service Bracket, Flow Sensor, Automatic Cleaning Module, SC200 Controller

What's included?

TU5400sc Turbidimeter, User Manual, Wall Mount, Vial Replacement Tool, Screw Set, Drying Cartridge, Flow Regulator, Service Bracket, Flow Sensor, Automatic Cleaning Module, SC200 Controller