



Acidification/Cleaning Unit for Amperometric Sensors

Product #: LZY051
ZAR Price: Contact Hach
Call for ship date

Many amperometric processes have optimal pH ranges in which they will be most accurate and produce the best results. Adding an acidification/cleaning unit onto instruments such as the CL10 sc can help to ensure that samples stay range that is favorable for measurement.

Specifications

Cable Length:	1 m digital
Depth panel:	107 mm
Flow:	Min 0.24, max. 1 mL/min
Fuse Rating:	T, 250 mA, 250V
Height Panel:	270 mm
Material:	Carboy: PEHD (high-density polyethylene)
Power requirements (Voltage):	12 VDC
Process Connection:	0.125 " NPT (for tube fittings)
Volume:	10 L chemicals not supplied
Warranty:	12 months
What's included?:	Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.
Width Panel:	250 mm

What's included?

Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.