



Flow through unit Nitratax clear sc, 5 mm

Product #: LZX866
ZAR Price: Contact Hach
Ships within 2 weeks

The through-flow variant is used wherever direct measurement in the medium is not possible for construction related reasons or the medium load makes it necessary to measure a filtered sample.

Specifications

Dimensions (H x W x D):	210 mm x 500 mm x 160 mm
Material:	Measuring cell: PVC; Glands: PVDF; Sample tube: PVC; Screws: Stainless Steel; Seals: EPDM
Operating temperature range:	2 - 40 °C (sample temperature)
Pressure Range:	Not pressurized, open drain
Sample Input:	Tube ID 4 mm/AD 6 mm
Sample Volume:	0.5 - 10 L
Weight:	3.6 kg
Wetted Materials:	Measuring cell: PVC; Seals: EPDM; Glands: PVDF; Sample tube: PVC