



High Output Airblast Cleaning System, 115 V

Product #:

6860000

ZAR Price:

Contact Hach

Ships within 1 week

The High Output Airblast Cleaning System (115V) is a compressor in an outdoor enclosure for the LDO and ISEsc. It supplies air to a cleaning head which is mounted in front of the sensor. The HOAB, along with a cleaning unit attached to a sensor, will keep the sensor head clean for longer operation time in difficult applications.

Outdoor

The High Output Airblast Cleaning System can be installed outdoors.

Cleaning head not included

A cleaning head is not included and needs to be ordered separately depending on sensor type

Specifications

Warranty:

12 months