



## Flow through unit 50 mm for Uvas plus sc probes

**Product #:** LZX868  
**ZAR Price:** Contact Hach

Suitable for media with very high TS contents, sewage treatment plant inlet, etc.

---

### Specifications

Cable Length:	10 m
Dimensions (H x W x D):	210 mm x 500 mm x 160 mm
Length:	33 mm
Operating temperature range:	2 - 40 °C (sample temperature)
Path Length:	2 mm
Pressure Range:	Not pressurized, open drain
Sample Flow Rate:	0.5 L/h
Sample Input:	Tube ID 4 mm / AD 6 mm
Sample Temperature:	2 - 40°C (35.6 - 104°F)
Sample Volume:	0.5 - 10 L
Weight:	3.6 kg