



## TSS Titanium2 sc, Suspended Solids Triclamp Inline Sensor without Wiper

**Product #:** LXV329.99.20002  
**ZAR Price:** Contact Hach  
**Call for ship date**

### Measures on-line suspended solids in virtually all applications under the strictest regulatory conditions.

Measures online suspended solids in aggressive or corrosive environments. Constructed of titanium to perform in the most extreme applications. Measures both online suspended solids and turbidity in one instrument. Includes bubble and temperature compensation software for a more accurate measurement. Connects directly to all Hach SC controllers for immediate use. TriClamp model provides simple inline installation and quick access for maintenance.

#### Unique Multi-Beam Pulsed Infrared Light System

TSS sc probes have a double optical system with two pulsating infrared LEDs and four receivers. This combined multiple beam alternating light method with beam focusing facilitates accurate color independent measurement of turbidity from 0.001 to 4,000 FNU and suspended solids from 0.001 to 500 g/L.

#### Automatic Compensation for Air Bubbles and Temperature Swings for Accuracy

Special software enables the system to recognize gas bubbles or temperature swings for a more accurate suspended solids or turbidity measurement.

#### Standard Compliant and Precise - Ease of Calibration

The turbidity measurement complies with the standard DIN EN 27027 (ISO 7027). Calibration is not necessary. If the probe is used to measure the solids content, a one-point calibration suffices. For special applications, curves can be defined using several calibration points.

#### The Only Titanium Suspended Solids Probe in the Market Designed for the Most Difficult Environments

While offering the same high quality measuring properties, its special titanium body enables it to perform in the most extreme applications.

---

## Specifications

Accuracy:	Turbidity up to 1000 NTU:  < 5% of the measured value $\pm 0.01$ NTU
Ambient Temperature:	0 - 60 °C (briefly 80 °C)
Application:	Aggressive media
Automatic Wiper:	No
Cable Length:	10 m (optional extension cables available)
Calibration:	Turbidity (TRB): Factory calibrated  Solids (TS): To be calibrated by customer on site  Zero point: Permanently calibrated in the factory
Calibration Method:	Turbidity Formazin or Stablcal Standard (at 800 NTU). Requires a calibration kit.  Suspended Solids Sample specific, based on gravimetric analysis with a correction factor procedure.
Controller Compatibility:	SC200, SC1000, SC4500. All controllers sold separately

Diameter:	40 mm
Flow:	Max. 3 m/s (the presence of air bubbles affects the measurement)
Includes:	Turbidity & Suspended Solids sensor, user manual
Installation style:	User Defined, with TriClamp
Length:	Tank sensor: 332 mm
Maintenance Interval:	1 h/month
Material:	Gasket: FKM; Wiper: PA (GF), TPV
Max Temperature:	60 °C
Measurement method:	Combined multiple beam alternating light method with infrared diode system and beam focusing
	<i>Turbidity</i> (TRB): 2-channel 90° scattered light measurement in accordance with DIN EN ISO 7027, wavelength = 860 nm
	<i>Solids</i> (TS): 90° and 120° scattered light measurement, wavelength = 860 nm
Measuring range:	Turbidity (TRB): 0.001 - 9999 NTU
	Solids (TSS): 0.001 - 500 g/L
Model:	TSS Titanium2 sc
Mounting Configurations:	TriClamp
Operating temperature range:	0 - 60 °C
Parameter:	Turbidity, Suspended Solids
Pressure Range:	<lte/> 10 bar or <lte/> 100 m
Repeatability:	TSS content: < 4 %
	Turbidity: < 3 %
Response time:	1 s < T90 < 300 s (adjustable)
Response Time T90:	1 - 300 s adjustable
Special Notes:	Installation note:
	Distance sensor–wall
	> 50 cm (Turbidity)
	> 10 cm (TSS)
Warranty:	12 months
Weight:	approx. 1.6 kg
What's included?:	Turbidity & Suspended Solids sensor, user manual

## What's included?

Turbidity & Suspended Solids sensor, user manual