



General Purpose Contacting Conductivity Sensor, PPS Body, High Conductivity (k=10.0)

Product #: 3433E8A
ZAR Price: Contact Hach
Ships within 3 days

Ultimate accuracy from ultra-pure to high conductivity applications.

Contacting conductivity sensor with a nominal cell constant $k = 10.0 \text{ cm}^{-1}$, $\frac{3}{4}$ -inch male NPT threaded PPS body, 6 m analogue cable, and graphite electrode.

Measuring range 0 - 200000 $\mu\text{S/cm}$.

High performance design

These sensors are manufactured to exacting tolerances using high quality, rugged materials for demanding applications including ultra-pure water, clean-in-place (CIP), and boiler/condensate monitoring. Each sensor is tested to determine its unique, absolute four-digit cell constant. Also, each sensor has a PT1000 RTD temperature element built into its tip for exceptionally fast response to changes in temperature with $\pm 0.1^\circ\text{C}$ accuracy.

Resistivity and conductivity measurement capability

These enhanced performance sensors measure from 0.057 $\mu\text{S/cm}$ or 18.2 $\text{M}\Omega$ (theoretically pure water) up to 200,000 $\mu\text{S/cm}$.

Versatile mounting styles

Non-Metallic General Purpose Sensors have graphite electrodes and $\frac{3}{4}$ -inch male NPT threaded PPS bodies. Mount into a standard $\frac{3}{4}$ -inch pipe tee, 1- $\frac{1}{2}$ -inch Hach union hardware (for cell constant $k=10$ sensor only), or fasten onto the end of the pipe.

Full-Featured “Plug and Play” Hach SC Digital Controllers

There are no complicated wiring or set up procedures with any Hach SC controller. Just plug in any combination of Hach digital sensors and it's ready to use—it's “plug and play.”

Specifications

Accuracy:	$\pm 2\%$ of reading above 200 $\mu\text{S/cm}$
Cable Length:	6 m
Cell constant k:	10 cm^{-1}
Diameter:	32.5 mm
Digital Gateway:	None
Electrode Material:	Graphite
Flow:	0 - 3 m/s maximum, fully immersed
Immersion Depth 2:	33 mm tee mount
Installation style:	General purpose
Junction box:	None
Length:	134.6 mm
Measuring range:	0 - 200000 $\mu\text{S/cm}$
Operating temperature range:	-20 - 200 $^\circ\text{C}$

Pressure Range:	6.8 bar at 150 °C (when used with hardware, a lower rated mounting hardware or piping material may limit the temperature and pressure ratings)
Repeatability:	±0.5 % of reading
Response Time T90:	< 30 s after step change
Sensitivity:	±0.5 % of reading
Sensor Immersion Depth:	114.3 mm pipe mount
Sensor Thread:	¾" NPT at both ends
Sensor Type :	Analog
Temperature Measurement:	-20 - 200 °C
Temperature Sensor :	PT1000 RTD
Transmission Distance:	100 m maximum;
	1000 m maximum, when used with a termination box
Warranty:	12 months
What's included?:	Includes: sensor with 6 m (20 ft) cable and manual

What's included?

Includes: sensor with 6 m (20 ft) cable and manual

Required Accessories

- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 100-240 VAC, US plug (Item LXV525.99E11551)
- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 100-240 VAC, without power cord (Item LXV525.99A11551)
- SC4500 Controller, Prognosys, 5x mA Output, 1 digital Sensor, 100-240 VAC, without power cord (Item LXV525.99A11501)
- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 24 VDC, without plug (Item LXV525.99Z11551)