



¾" Combination pH Sensor, Insertion Style, PVDF, Flat Glass pH Electrode, PT1000, 4.5 m Cable

Product #: PC2K2A
ZAR Price: Contact Hach
Ships within 3-5 weeks

PVDF, insertion body style, 4.5 m analog cable, flat glass pH electrode, PT1000 temperature compensation

Low Price - Great Performance

These combination sensors are designed for specialty applications for immersion or in-line mounting. The reference cell features a double-junction design for extended service life, and a built-in solution ground. The body is molded from chemically-resistant PPS or PVDF, and the reference junction is coaxial porous PTFE. All sensors are rated 0 to 105 °C up to 100 psig, and have integral 4.5 m (15 ft.) cables with tinned leads. The PC-series (for pH) and RC-series (for ORP) combination sensors are ideal for measuring mild and aggressive media.

Special Electrode Configurations

Sensors with rugged dome electrodes, “easy-to-clean” flat glass electrodes, and even HF (hydrofluoric acid) resistant glass electrodes are available for a wide variety of process solutions.

Temperature Compensation Element Option

The PC-series combination pH sensors are available with or without a PT1000 ohm RTD temperature element. The RC-series combination ORP sensors are supplied without a temperature element.

Versatile Mounting Styles

Sensors are available in three mounting styles - convertible, insertion, and sanitary.

Full-Featured “Plug and Play” Hach Digital SC Controllers

There are no complicated wiring or set up procedures with any Hach SC controller. Just plug in any combination of Hach digital sensors and it's ready to use-it's “plug and play.” One or multiple sensors-the SC controller family allows you to receive data from up to eight Hach digital sensors in any combination using a single controller.

Specifications

Accuracy:	± 0.1 pH under reference conditions
Body material:	PVDF/316 SS
Cable Length:	4.5 m fixed cable, terminated with stripped and tinned wires
Diameter:	33 mm
Electrode Type:	Insertion
Flow:	0 - 2 m/s
Length:	149.9 mm
Material:	Flat glass
Measuring range:	0 - 14 pH
Operating temperature range:	0 - 105 °C
Parameter:	pH
Pressure Range:	6.9 bar at 100 °C
Sensor Thread:	0.75" NPT on both ends

Temperature Compensation:	Yes
Transmission Distance:	100 m (328 ft.), maximum
Transmission Distance 2:	1000 m (3280 ft.), maximum when used with a termination box
Warranty:	3 months
Wetted Materials:	PVDF, PTFE double junction, glass electrode, FKM/FPM O-rings
What's included?:	Includes: sensor with 15 ft cable and manual

What's included?

Includes: sensor with 15 ft cable and manual