



Hach Online Process ORP Sensor - General Purpose Analog ORP Sensor

Product #: RD1P5A50
ZAR Price: Contact Hach
Ships within 1 week

The smart choice for accurate and reliable online process ORP measurement

General Purpose Online Process ORP Sensor - Platinum ORP Electrode, PEEK Housing, Convertible Mount, 50 ft Cable, Analog Cable Connection

Exceptional Performance with the Differential Electrode Measurement Technique

This field-proven technique uses three electrodes instead of the two normally used in conventional ORP sensors. Process and reference electrodes measure the ORP differentially with respect to a third ground electrode. The end result is unsurpassed measurement accuracy, reduced reference junction potential, and elimination of sensor ground loops. These sensors provide greater reliability, resulting in less downtime and maintenance.

Lower Maintenance Needs with the Double Junction Salt Bridge

The double junction salt bridge creates a barrier to contamination which minimizes the dilution of the internal standard cell solution. The result is lower maintenance needs and a longer time period between calibrations.

Extended Working Life with the Replaceable Salt Bridge/Protector

The unique, replaceable salt bridge holds an extraordinary volume of buffer to extend the working life of the sensor by protecting the reference electrode from harsh process conditions. The salt bridge simply threads onto the end of the sensor if replacement is needed.

Reliability with Built-in Encapsulated Preamp

Encapsulated construction protects the sensor's built-in preamp from moisture and humidity, ensuring reliable sensor operation. The preamp in the pHD analog sensor produces a strong signal, enabling the sensor to be located up to 1000 m (3280 ft.) from the analyzer.

Patented Technology

The former GLI, now a Hach Company brand, invented the Differential Electrode Technique for pH measurement in 1970. The pH^D™ sensor series (U.S. Patent Number 6395158B1, dated May 28, 2002) takes this field-proven technology to a new level.

Specifications

Body material:	PEEK
Body Material:	PEEK
Cable Connection:	Analog
Cable Length:	15 m
Electrode Material:	Platinum
Electrode Type:	General Purpose
Mounting:	Convertible
Sensor Type :	Analog
Warranty:	12 months