



## Hach pH<sup>®</sup>D Online Process pH Sensor - pH Sensor for Clean Water

Product #:

PD1R1.99

ZAR Price:

Contact Hach

### The smart choice for accurate and reliable online process pH measurement

Clean Water Online Process pH Sensor - pH<sup>®</sup>D Technology, Glass pH Electrode, PPS Housing, Convertible Mount, 4.5 m Cable

#### Exceptional Process pH Sensor Performance with the Differential Electrode pH<sup>®</sup>D Measurement Technique

This field-proven technique uses three electrodes instead of the two normally used in conventional pH sensors. Process and reference electrodes measure the pH differentially with respect to a third ground electrode. The end result is unsurpassed measurement accuracy, reduced reference junction potential, and elimination of sensor ground loops. These process pH sensors provide greater reliability, resulting in less downtime and maintenance.

#### Lower Maintenance Needs with the Double Junction Salt Bridge

The double junction salt bridge creates a barrier to contamination which minimizes the dilution of the internal standard cell solution. The result is lower maintenance needs and a longer time period between calibrations.

#### Extended Working Life with the Replaceable Salt Bridge/Protector

The unique, replaceable salt bridge holds an extraordinary volume of buffer to extend the working life of the sensor by protecting the reference electrode from harsh process conditions. The salt bridge simply threads onto the end of the sensor if replacement is needed.

#### Reliability with Built-in Encapsulated Preamp

Encapsulated construction protects the sensor's built-in preamp from moisture and humidity, ensuring reliable sensor operation. The preamp in the pH<sup>®</sup>D analogue sensor produces a strong signal, enabling the sensor to be located up to 1000 m (3280 ft.) from the analyser.

#### Innovative Technology

The former GLI, now a Hach Company brand, invented the Differential Electrode Technique for pH measurement in 1970. The pH<sup>®</sup>D sensor series takes this field-proven technology to a new level.

---

## Specifications

Accuracy:	± 0.02 pH
Body material:	PPS
Cable Connection:	Analog
Cable Length:	6 m PUR (polyurethane) 4-conductor with one shield, rated to 105 °C
Calibration Method:	Two point automatic, one point automatic, two point manual, one point manual.
Diameter:	34.9 mm
Drift:	0.03 pH per 24 hours, non-cumulative
Electrode Type:	General Purpose
Flow:	max. 3 m
Length:	196.3 mm
Material:	Ground Electrode: Titanium
Measuring range:	-2.0 - 14.0 pH
Mounting:	Convertible

Operating temperature range:	-5 - 105 °C
Pressure Range:	max. 10.7 bar Sensor only (pressure range of mounting hardware to be checked separately)
Repeatability:	± 0.05 pH
Sensor Thread:	1" NPT at both ends
Special Notes:	pH-Wide Range Generic
Temperature Accuracy:	± 0.5 °C
Temperature Compensation:	Automatic with NTC 300 Ω thermistor, or manually fixed at a user-entered temperature,  additional selectable temperature correction factors (ammonia, morpholine, or user-defined pH/°C linear slope) available for pure water automatic compensation 0.0 - 50 °C
Temperature Sensor :	NTC 300 Ω thermistor for automatic temperature compensation and analyzer temperature readout
Warranty:	12 months
Weight:	0.9534 kg

---

## Required Accessories

- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 100-240 VAC, US plug (Item LXV525.99E11551)
- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 100-240 VAC, without power cord (Item LXV525.99A11551)
- SC4500 Controller, Prognosys, 5x mA Output, 1 digital Sensor, 100-240 VAC, without power cord (Item LXV525.99A11501)
- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 24 VDC, without plug (Item LXV525.99Z11551)