



Hach pH Online Process pH Sensor - General Purpose Insertion Mount pH Sensor

Product #: PD2P1.99
ZAR Price: Contact Hach

The smart choice for accurate and reliable online process pH measurement

General Purpose Online Process pH Sensor - pH Technology, Glass pH Electrode, PEEK Housing, Insertion Mount, 4.5 m Cable

Exceptional Process pH Sensor Performance with the Differential Electrode pH Measurement Technique

This field-proven technique uses three electrodes instead of the two normally used in conventional pH sensors. Process and reference electrodes measure the pH differentially with respect to a third ground electrode. The end result is unsurpassed measurement accuracy, reduced reference junction potential, and elimination of sensor ground loops. These process pH sensors provide greater reliability, resulting in less downtime and maintenance.

Lower Maintenance Needs with the Double Junction Salt Bridge

The double junction salt bridge creates a barrier to contamination which minimizes the dilution of the internal standard cell solution. The result is lower maintenance needs and a longer time period between calibrations.

Extended Working Life with the Replaceable Salt Bridge/Protector

The unique, replaceable salt bridge holds an extraordinary volume of buffer to extend the working life of the sensor by protecting the reference electrode from harsh process conditions. The salt bridge simply threads onto the end of the sensor if replacement is needed.

Reliability with Built-in Encapsulated Preamp

Encapsulated construction protects the sensor's built-in preamp from moisture and humidity, ensuring reliable sensor operation. The preamp in the pHD analogue sensor produces a strong signal, enabling the sensor to be located up to 1000 m (3280 ft.) from the analyser.

Innovative Technology

The former GLI, now a Hach Company brand, invented the Differential Electrode Technique for pH measurement in 1970. The pHD sensor series takes this field-proven technology to a new level.

Specifications

Body material:	PEEK
Cable Connection:	Analog
Cable Length:	4.5 m
Electrode Type:	General Purpose
Mounting:	Insertion
Special Notes:	pH-Wide Range Generic
Warranty:	12 months

Required Accessories

- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 100-240 VAC, US plug (Item LXV525.99E11551)
- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 100-240 VAC, without power cord (Item LXV525.99A11551)
- SC4500 Controller, Prognosys, 5x mA Output, 1 digital Sensor, 100-240 VAC, without power cord (Item LXV525.99A11501)
- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 24 VDC, without plug (Item LXV525.99Z11551)