



## Replacement salt bridge for pH sensor, outer-junction, PPS Salt Bridge, PVDF

**Product #:**

**SB-R1SV**

**ZAR Price:**

Contact Hach

Ships within 1 week

### Lowest Lifetime Cost of Process pH Sensors

The double junction salt bridge on all Hach pHDTM Differential pH / ORP Sensors is field-replaceable, and includes a FKM/FPM O-ring. Salt bridges are shipped in a salt solution to prevent dehydration / dry-out and can be stored in the shipping solution until needed. Salt bridges are available in a variety of materials and pre-packaged quantities.

---

### Specifications

Material:	PPS
Special Notes:	The double junction salt bridge is field-replaceable.
Special notes:	Each salt bridge has a ceramic inner junction, FKM/FPM O-ring, and contains binary, equi-transferrant fill solution. (Salt bridges are shipped in a salt solution.)