



pH Sensor, PPS Body, 2 Wire, Convertible style, FKM/FPM Seals, 10-ft Cable

Product #:

6422P0

ZAR Price:

Contact Hach

Ships within 1 week

Regenerateable Encapsulated LCP or PPS Differential pH and ORP Sensors-ideal for aggressive applications.

PPS, Convertible Mounting Style, 3m Analog Cable, 2-Wire with Built-In Transmitter, General Purpose Glass pH Electrode

Exceptional Performance with the Differential Electrode Measurement Technique

This field-proven technique uses three electrodes instead of the two normally used in conventional pH sensors. Process and reference electrodes measure the pH differentially with respect to a third ground electrode. The end result is unsurpassed measurement accuracy, reduced reference junction potential, and elimination of sensor ground loops. These sensors provide greater reliability, resulting in less downtime and maintenance.

Lower Maintenance Needs with the Replaceable Salt Bridge

The salt bridge creates a barrier to contamination which minimizes the dilution of the internal standard cell solution. The result is lower maintenance needs and a longer time period between calibrations.

Built-in Preamp or Two-Wire Transmitter

The built-in preamp produces a strong signal, enabling you to locate the analyzer up to 3000 ft. (914 m) from the sensor. An optional built-in two-wire transmitter is available for applications requiring a 4-20 mA sensor signal. This option requires that the indicating instrument of the measuring system be capable of providing 24 VDC to power the sensor, and have adjustment means to calibrate for zero offset and span.

Versatile Mounting Styles

1.5 inch NPT threads are provided on both ends of the convertible mounting style sensor for either mounting into a pipe tee or attaching to the end of a pipe for immersion. The convertible style enables you to consolidate inventory, and thereby reduce associated costs. A union-mount style sensor and mounting tee are also available to conveniently install and remove the sensor for in-line service.

3,000 ft. (914 m) transmission distance

Specifications

Body material:	PPS
Cable Length:	3 m (10 ft)
Diameter:	55 mm
Electrode Material:	Glass
Junction:	PVDF Junction
Measuring Range ORP:	-2000 - +2000 mV
Measuring range pH:	0 - 14 pH
Mounting:	Convertible
Sensitivity:	< 0.005 pH
Sensitivity 2:	< 0.5 mV
Temperature Range:	-5 - 95 °C (23 - 203 °F)
Weight:	0.6 kg

What's included?:

Includes: sensor with 3 m (10 ft) cable and manual

What's included?

Includes: sensor with 3 m (10 ft) cable and manual