



D.O. Mounting, Flootation

Product #:	MH276J00F
ZAR Price:	Contact Hach
Ships within 2 weeks	

Flotation Mounting Hardware Hardware consists of a 1-1/2 inch diameter by 7.5 foot (2.3m) long PVC pipe, a unique swivel/ pivot/pipe clamp assembly, and a surface-mount NEMA 4X junction box with quick-disconnect receptacle for sensor with metal plug on cable end. It also includes also includes a ball float assembly, and a 45°-angled PVC coupling to connect the float assembly to the pipe