



Finished Sensor, Insertion Type, Brass Tee

Product #:	F1A13D1T
ZAR Price:	Contact Hach
Ships within 1 week	

Brass Sleeved PVDF Body with 2-Inch NPT Adapter to fasten into MHF21A0 Ball Valve Assembly, Hot Tap Mounting Style, 6m (20ft) Analog Cable

Non-magnetic sensing technique

Variable frequency square wave signal

Wide rangeability

Superior low-velocity performance

Specifications

Body material:	Brass sleeved PVDF
Cable Length:	20
Mounting:	Ball Valve Assembly, Hot Tap
Warranty:	12 months
What's included?:	Includes: sensor with 20 ft cable and manual

What's included?

Includes: sensor with 20 ft cable and manual