



Polypropylene Flow Sensor, Tee Mount, 50 ft Analog Cable

Product #: F1A11A1T50
ZAR Price: Contact Hach
Ships within 2 weeks

Polypropylene Material, Tee-Mount Style Impeller Flow Sensor, 15m (50ft) Analog Cable

Economical and practical

Used with a controller, you can independently monitor four sensors with convenience.

Non-magnetic sensing technique

Hach's Impeller Flow sensors unique non-magnetic sensing technique is impervious to fouling from metal particles. The non-magnetic sensing technique reduces drag for superior low-flow and low-volume measurement accuracy.

Superior low-velocity performance

The forward-swept, six-bladed impeller has significantly better low-flow, low-velocity characteristics than conventional four-bladed impellers to provide higher measuring accuracy.

Wide rangeability

Variable frequency square wave signal

Specifications

Body material:	Polypropylene
Cable Length:	50
Mounting:	Tee mount
Warranty:	12 months
What's included?:	Includes: sensor with 50 ft cable and manual

What's included?

Includes: sensor with 50 ft cable and manual