



Stainless Steel Hot Tap Flow Sensor

Product #: F1A13C1T
ZAR Price: Contact Hach
Ships within 1 week

316 Stainless Steel Sleeved PVDF Body with 2-Inch NPT Adapter to fasten into MHF21A0 Ball Valve Assembly, Hot Tap Mounting Style, 6m (20ft) Analog Cable

Non-magnetic sensing technique

Variable frequency square wave signal

Wide rangeability

Superior low-velocity performance

Specifications

Body material:	Stainless steel sleeved PVDF
Cable Length:	20
Mounting:	Pipe thread/hot tap
Warranty:	12 months
What's included?:	Includes: sensor with 20 ft cable and manual

What's included?

Includes: sensor with 20 ft cable and manual