



Flow Sensor, Stainless Steel, PVDF Body, 40 ft Cable

Product #: F1A12C1T40
ZAR Price: Contact Hach
Ships within 2 weeks

Pipe Thread/316 Stainless Steel Sleeved PVDF Body with 2-Inch NPT Hex Mounting Adapter to Pipe Tee or Weld Saddle, Pipe Thread Insertion Mount Style, 12m (40ft) Analog Cable

Non-magnetic sensing technique

Variable frequency square wave signal

Wide rangeability

Superior low-velocity performance

Specifications

Body material:	Stainless steel sleeved PVDF & paper tag ID
Cable Length:	40
Mounting:	Pipe thread/hot tap
Warranty:	12 months
What's included?:	Includes: sensor with 40 ft cable and manual

What's included?

Includes: sensor with 40 ft cable and manual