



*Be Right™*



## **ETFE membranes for use with electrochemical sensors, 25 $\mu$ m, 35 mm diameter, box of 25**

|                   |              |
|-------------------|--------------|
| <b>Product #:</b> | <b>2952A</b> |
| ZAR Price:        | Contact Hach |
| Available         |              |

---

### **Specifications**

|                        |            |
|------------------------|------------|
| Material:              | ETFE       |
| Membrane Thickness:    | 25 $\mu$ m |
| Radiation Dose Limits: | 108 rad    |