



Orbisphere 410 Controller O₃ (EC), Panel Mount, 10-30 VDC, 0/4-20mA, Profibus

Product #: 410C/P2C10000

ZAR Price: Contact Hach

Precise, Powerful Process monitoring

The Orbisphere 410 Mono-Channel controller offers precise, powerful process monitoring capability.

Designed to complement the Orbisphere high quality sensors these instruments provide accurate, repeatable trace level measurements and an impressive level of data management.

Depending on the version, the Orbisphere 410 controller can be combined with:

- Orbisphere 311xx Oxygen Sensors
- Orbisphere A1100 Oxygen Sensors
- Orbisphere K1100 Oxygen Sensors
- Orbisphere M1100 Oxygen Sensor
- Orbisphere 314xx Carbon Dioxide Sensors
- Orbisphere C1100 Ozone Sensors

These controllers are designed for applications in the power generation, electronics, life sciences, beverage, chemical and water treatment industries.

Do not hesitate to contact us to define the best configuration for your application.

Easy to use, intuitive software using clear, full color touch-screen

All functions of Orbisphere 410 instruments are accessed through the color, touch screen. This screen acts as display and keyboard.

Internal diagnostics and reminders for maintenance and calibration

To ensure continuous high performance and simplify maintenance, Orbisphere 510 instruments offer a number of diagnostic features.

- Notification that calibration is due—ensures QC procedural compliance
- Notification that a sensor service is due—optimal preventative maintenance planning
- Sensor service diagnostics—minimizes downtime

- System alarms transmitted through analog output—continuous status indication

Easy to use and reliable

Orbisphere 410 instruments are designed for ease of use. After simple installation, the system is measuring your process in minutes. Simple menus allow you to rapidly create a specific configuration for the instrument. The main measurement window continuously displays real time process readings, graphed sensor trends (user selectable from last 1 minute to last 1 hour), alarm limits, temperature and event occurrence.

Multiple communication options including USB and Profibus

Digital communication uses industry standard protocols including Profibus and USB in addition to traditional analog outputs and alarm relays. These may all be configured in terms of function, content and behavior.

Data Storage

Data storage of up to 10000 measurements, last 1000 operator actions and details of last 50 calibrations

Specifications

Accuracy:	Accuracy: ± 0.5% (between operating temperature limits)
Analogue Outputs:	3 smart 0/4-20 mA (500 ohms), programmable as linear or tri-linear, configurable to send diagnostics information
Communication:	3 x 0/4-20 mA; RS485; Ethernet; Profibus
Communication Capabilities:	3 x 0/4-20 mA; RS485; Ethernet
Compatible Instruments:	Channel 1 : 313xx or C1100
Compliance Certifications:	EMC: EN61326-1:2006
	CE: EN61010-1:2010
	ETL, conforming to UL 61010-1 and CSA 22.2 No. 61010-1
Controller:	410, Mono-channel
Data storage:	Rolling buffer or store once mode for up to 1000 measurements and 1000 operator actions
	Holds calibration records for last 50 calibrations
Dimensions (H x W x D):	156 mm x 220 mm x 253.5 mm
Display:	Colour TFT touchscreen display
Electrode Compatibility:	Channel 1 : 313xx or C1100
Enclosure Construction:	Panel Mount
Material:	Aluminum
Measurements:	Resolution, accuracy and response time are determined by sensor
Number of Channels:	1
Operating conditions:	0 - 95 % non-condensing relative humidity
Operating temperature range:	-5 - 50 °C
Parameter:	O ₂ (EC)
Password Protection:	5 levels of authorised access to configuration and data management
Power:	10 to 30 VDC - 30W
Power requirements (Voltage):	10 - 30 VDC
Power supply:	10 to 30 VDC - 30W
Relays:	3 measurement alarm relays (2A to 30 VAC or 0.5 A to 50 VDC); configurable to send diagnostics information
	1 system alarm relay (2 A to 30 VAC or 0.5 A to 50 VDC)
Units:	• Gas concentration: Configurable for gas or liquid phase with multiple unit options
	• Pressure : External and barometric pressure with multiple unit options

	• Temperature : Sample temperature with unit options (K, °C, °F)
User Interface:	Touch screen panel displays: concentration, trend graph, diagnostics, alarm status, historical data
Weight:	2.9 kg
What's included?:	410 controller and manual only. Sensor and cable, flow-chamber or process connection, must be ordered separately.

What's included?

410 controller and manual only. Sensor and cable, flow-chamber or process connection, must be ordered separately.