



## Tee, Sanitary Clamp, Ss316L

<b>Product #:</b>	<b>9H1310</b>
ZAR Price:	Contact Hach
Call for ship date	

2-inch Sanitary Tee for 3455-series and PC/RC series sensors. Stainless Steel 316 L Material.

### Low Price & High Performance

These combination sensors are designed for specialty applications for immersion or in-line mounting. The reference cell features a double-junction design for extended service life, and a built-in solution ground. The body is molded from chemically-resistant

### Special Electrode Configurations

Sensors with rugged dome electrodes, & easy-to-clean flat glass electrodes, and even HF (hydrofluoric acid) resistant glass electrodes are available for a wide variety of process solutions.

### Temperature Compensation Element Option

The PC-series combination pH sensors are available with or without a Pt 1000 ohm RTD temperature element. The RC-series combination ORP sensors are supplied without a temperature element.

### Versatile Mounting Styles

Sensors are available in three mounting styles—convertible, insertion, and sanitary.

### Full-Featured & Plug and Play Hach sc Digital Controllers

There are no complicated wiring or set up procedures with any Hach sc controller. Just plug in any combination of Hach digital sensors and it's ready to use. & plug and play. <TableBullet/> One or multiple sensors & The sc controller family