



DR300 Pocket Colorimeter, 500 nm, with Box

Product #: LPV445.97.50110

ZAR Price: Contact Hach

Proven past. Accurate and Fast.

The DR300 maintains the Hach Pocket Colorimeter legacy of reliability with a more user friendly design.

Please note that reagents are not included in the kit and need to be purchased separately.

Reliable

Since 1993, Hach has continued to provide premium chemistries and colorimetry instrumentation, providing dependable, accurate measurements.

Simple

Simple, intuitive operation reduces potential manual error, ensuring accurate measurement data you can trust, time after time. Larger display with improved backlight makes reading measurements in all conditions even easier.

Durable

Rugged, waterproof (IP67) design withstands whatever conditions you encounter in the field or on the road (drops, extreme temperatures, rain and dirt).

Specifications

Absorbance:	0 - 2.5 Abs
Data Logger:	Last 50 measurements
Detector:	Silicon photodiode
Dimensions (H x W x D):	34 mm x 69 mm x 157 mm
Display:	LCD with backlight
Enclosure rating:	IP67, waterproof at 1 m for 30 minutes
Operating conditions:	0 - 50 °C; 0 - 90% relative humidity (non-condensing)
Power supply:	Four AAA alkaline batteries; approximate life is 5000 tests
Sample cell compatibility:	1 cm (10 mL), 25 mm (10 mL)
Source Lamp:	Light emitting diode (LED)
Special Features:	With Box
Spectral Bandwidth:	15 nm filter bandwidth
Warranty:	12 months
Wavelength:	500 ±2 nm

Weight:	0.25 kg
What's included?:	Each DR300 Pocket Colorimeter comes as a ready-to-use kit in a sturdy custom carrying case (4660200), including batteries, sample cells (2427606), and a manual. Reagents have to be purchased separately.

What's included?

Each DR300 Pocket Colorimeter comes as a ready-to-use kit in a sturdy custom carrying case (4660200), including batteries, sample cells (2427606), and a manual. Reagents have to be purchased separately.