



Polymetron 9500 Controller, 100 - 240 VAC, two conductivity inputs, Modbus 232/485, two 4 - 20 mA outputs

Product #: 9500.99.01664

ZAR Price: Contact Hach

One controller for a broad range of sensors.

A complete water analytics system designed for the Power industry. Hach provides a broad range of product options made to work together as flexible solutions to meet your unique needs. The comprehensive approach saves you time on design, installation, training, maintenance, and operation.

Save time on design

A single design source and one product platform means you spend less time searching for design files or configuring components. Create and reuse your optimal design templates.

Accelerate your installation

One source, interchangeable components, a common user interface, and one support team make installation faster and less complicated. Quickly and easily transfer user settings between controllers.

Reduce training complexity

A single platform minimises time required to teach and learn product operations, getting new systems in use faster.

Simplify maintenance and operation

Common menu guides reduce variability and provide step-by-step procedures for maintenance and calibration. Standard visual alerts across parameters notify operators when troubleshooting is required.

Specifications

Analogue Outputs:	Two (Five with optional expansion module) 0/4 to 20 mA isolated current outputs, max. 550 Ω , Accuracy: $\pm 0.1\%$ of FS (20 mA) at 25 °C, $\pm 0.5\%$ of FS over -20 °C to 60 °C range
Communication Capabilities:	Modbus RS232/RS485
Conduit Openings:	1/2" NPT Conduit
Display:	Graphic dot matrix LCD with LED backlighting, transreflective
Display Resolution:	240 x 160 pixels
Display Size:	48 x 68 mm
Electrical Certifications:	EMC CE compliant for conducted and radiated emissions: - CISPR 11 (Class A limits) - EMC Immunity EN 61326-1 (Industrial limits)
Enclosure rating:	IP66 / NEMA 4X
Mounting Configurations:	Wall

	Pole
	Panel Mounting
Operating temperature range:	-20 - 60 °C at 0 - 95% RH (non-condensing)
Power Options:	100 - 240 V, no power cord
Power requirements (Hz):	50 - 60 Hz
Power requirements (Voltage):	100 - 240 VAC
Relays:	Four electromechanical SPDT (Form C) contacts, 1200 W, 5 A
Security levels:	2
Sensor Input #1:	Conductivity
Sensor Input #2:	Conductivity
Warranty:	12 months
Weight:	1.70 kg
What's included?:	Controller, mounting hardware, basic user manual

What's included?

Controller, mounting hardware, basic user manual