



## Polymetron 9582 Dissolved Oxygen System with 4-20 mA Output Communications, 100 - 240 V AC

Product #: 9582.99.09P4  
ZAR Price: Contact Hach



**Hazardous**

Items with this mark may be considered hazardous under some shipping conditions.

If necessary, we will change your selected shipping method to accomodate these items.

An integral part of the most complete water analytics system for the Power industry. Hach provides a broad range of product options designed to work together into flexible solutions to meet your unique needs. The comprehensive approach saves you time on design, installation, training, maintenance, and operation.

### Save Time on Design

A single design source and one product platform means you spend less time searching for design files or configuring components. Create and reuse your optimal design templates.

### Accelerate Your Installation

One source, interchangeable electronic components, a common user interface, and one support team make installation faster and less complicated. Quickly and easily transfer user settings between dissolved oxygen loops.

### Reduce Training Complexity

A single platform minimises time required to teach and learn product operations, getting new systems in use faster.

### Simplify Maintenance and Operation

Common menu guides reduce variability and provide step-by-step procedures for maintenance and calibration. Standard visual alerts across parameters notify operators when troubleshooting is required. Start-up and maintenance time are minimised with pre-mounted membrane cap and factory pre-conditioned sensors.

---

## Specifications

Cable Length:	10 m (33 ft)
Calibration Method:	Zero: Electrically or with oxygen free water, Slope: in air or against a laboratory measurement
Communication Capabilities:	5x 4-20 mA Out
Communication: digital:	MODBUS RS232/RS485, PROFIBUS DPV1, HART optional
Conduit Openings:	1/2" NPT Conduit
Connection Drain Line:	8 mm tubing
Connection Sample Line:	1/4" NPT thread (6mm or 1/4" tubing advised)
Display:	Graphic dot matrix LCD with LED backlighting, transreflective
Display Resolution:	240 x 160 pixels
Display Size:	48 x 68 mm
Electrical Certifications:	EMC
	CE compliant for conducted and radiated emissions:

- CISPR 11 (Class A limits)
- EMC Immunity EN 61326-1 (Industrial limits)

#### Safety

CAN/CSA C22.2 No. 61010-1

Enclosure rating:

IP66 / NEMA 4X

Lowest Detection Limit :

< 1 ppb

Maintenance Interval:

Membrane Lifetime: 6 months depending on sample

Manual Languages:

Bulgarian, Chinese (PRC), Croatian, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Lithuanian, Polish, Portuguese (Brazil), Portuguese (Portugal), Romanian, Russian, Slovak, Slovenian, Spanish, Swedish, Thai, Turkish

Material:

Electrodes: Gold cathode, Silver anode; Flow-through cell: Stainless Steel 316L; Membrane: PFA, Sensor Body: Noryl

Material Enclosures:

Polycarbonate

Aluminium (powder coated)

Stainless Steel

Measurements:

0 to 2000 ppb (0-2 ppm)

Measuring range:

0 - 2000 ppb (0-2 ppm)

Operating temperature range:

-20 - 60 °C at 0 - 95% RH (non-condensing)

Power requirements (Hz):

50/60 Hz

Power requirements (Voltage):

100 - 240 VAC

Range:

0 - 2000 ppb

Relay functions:

Scheduler (Timer), Alarm, Feeder Control, Event Control, Pulse Width Modulation, Frequency Control, and Warning

Relay: Operational mode:

Primary or secondary measurement, calculated value (dual channel only) or timer/scheduler

Relays:

Four electromechanical SPDT (Form C) contacts, 1200 W, 5 A

Repeatability:

± 0.5 ppb or ±5%, whichever is greater

Reproducibility:

± 0.5 ppb or ± 2% whichever is greater

Response Time:

For step change 1-40 ppb: <30s

Sample Flow Rate:

66 - 166

Security levels:

2

Storage conditions:

-20 °C - 70 °C

Temperature Compensation:

Automatic in the range of 0 - 45 °C (32 - 113 °F)

Units:

mg/L, ppm, µg/L, ppb, mbar, hPa, inch Hg, mmHg

Weight:

3.2 kg

What's included?:

Controller, mounting hardware, oxygen sensor, temperature sensor, cable, flow-chamber, basic user manual

---

## What's included?

Controller, mounting hardware, oxygen sensor, temperature sensor, cable, flow-chamber, basic user manual