



Polymetron 8417B 12 mm pH combination electrode, S7 connector

Product #: 368417,00000
ZAR Price: Contact Hach

Combination electrode with sealed reference design. Refillable, double junction with gelified electrolyte KCl. Suitable for high pressure and high temperature processes.

Specifications

Application:	High Temperature
Cable Connection:	S7 connector
Connector:	S7 Connector
Drift:	0.02 over 24 hours (T, P constant)
Length:	120 mm
Measuring range:	2 - 14 pH
Operating temperature range:	-5 - 120 °C
Pressure Range:	max. 10 bar at 25 °C
Reference electrode:	Ag/AgCl
Response time:	< 15 s at 25 °C
Temperature Sensor :	None